



FHS Clix S

| Artikelbezeichnung | Art.-Nr. | Max. empfohlene zentr. Zuglast für FUS 1,5 mm | Max. empfohlene zentr. Zuglast für FUS 2,0 mm | Max. empfohlene zentr. Zuglast für FUS 2,5 mm | Anzugsdrehmoment |
|--------------------|----------|--|--|--|--------------------|
| | | N_{empf} [kN] | N_{empf} [kN] | N_{empf} [kN] | T_{inst} [Nm] |
| FHS CLIX S 8 x 30 | 020914 | 3,0 | 4,0 | 4,0 | 5 |
| FHS CLIX S 8 x 40 | 020915 | 3,0 | 4,0 | 4,0 | 5 |
| FHS CLIX S 8 x 60 | 020916 | 3,0 | 4,0 | 4,0 | 5 |
| FHS CLIX S 10 x 30 | 020917 | 3,0 | 4,0 | 5,0 | 10 |
| FHS CLIX S 10 x 40 | 020918 | 3,0 | 4,0 | 5,0 | 10 |
| FHS CLIX S 10 x 60 | 020919 | 3,0 | 4,0 | 5,0 | 10 |
| FHS CLIX S 12 x 30 | 020969 | 3,0 | 4,0 | 5,0 | 10 |
| FHS CLIX S 12 x 40 | 047316 | 3,0 | 4,0 | 5,0 | 10 |
| FHS CLIX S 12 x 60 | 504320 | 3,0 | 4,0 | 5,0 | 10 |